

## Manual (Hand) Tape Casting Jig (Dual Blade Type)


(Model : MTC-01A)

開發	MANUAL TAPE CASTER Model MCT-01A	Ceramics green sheet
	Sheet	製作
MANUAL TAPE CASTER	Thickness Gauge	Dr. blade
, 가	Green Sheet	, blade
,	가	,

**Applications :** PTC SENSOR & HEATER 研究 . PZT .  
 NTC THERMISTOR SENSOR 研究 ,  
 R & D Works for Multi-layer Ceramics Package .,  
 MLCC , Chip Inductor , LTCC, Multi-layered RF module  
 . Multi-layered thick film sensor

### Machine Specification (Model MCT-01A)

1. 가 GREEN SHEET : 80 or 100 mm ( 가 .)
2. 가 GREEN SHEET Control 가 : 0 - 500 micron
3. : Thickness gauge .



**MANUFACTURER :**

**SALES :**

( )

1 407-5

TEL : 02-2249-5235

FAX : 02-2246-5946

E-MAIL : [ehansung@hotmail.com](mailto:ehansung@hotmail.com)



**MANUAL (HAND) TAPE CASTING JIG (Model MTC-01A and THICKNESS GAUGE**

## Dual Dr. Blade (for STC-14A Tape Casting Machine)

(Model : MTC-02A)

開發 Dual Dr. Blade Model MCT-02A Tape Casting Machine  
 Model STC-14A, STC-14C Sheet  
 製作  
 Model MCT-02A 4 Dial Gauge 가 blade  
 , 가 Green Sheet , 가

Applications : PTC SENSOR & HEATER 研究 . PZT .  
 NTC THERMISTOR SENSOR 研究 ,  
 R & D Works for Multi-layer Ceramics Package .,  
 MLCC , Chip Inductor , LTCC, Multi-layered RF module  
 . Multi-layered thick film sensor

### Machine Specification (Model MCT-02A)

- 4. 가 GREEN SHEET : 170 mm ( 가 .)
- 5. 가 GREEN SHEET Control 가 : 0 - 500 micron
- 6. : Dial Gauge . (10 micron 가 .)  
 ) (option : 1 micron 가 .)



<p><b><u>MANUFACTURER :</u></b></p> <p>( )</p> <p style="text-align: center;">407-5</p> <p>TEL : 02-2249-5235              FAX : 02-2246-5946              E-MAIL : <a href="mailto:ehansung@hotmail.com">ehansung@hotmail.com</a></p>	<p><b><u>SALES :</u></b></p>
--	------------------------------

CAT No. 020405K



DUAL Dr. Blade Model MTC-02A